

CONTRAST INJECTION LINES

Company Name	Product Name	Material	PSI Rating	ID/OD (inch)	Flexibility	Clarity	Length (inch)	Fittings
B. Braun	PVC High-Pressure Injection Lines	PVC	1,000	0.089 ID	Medium	High	10, 20, 30, 48	FLL/MLL connectors, FLL/rotating MLL connectors
	Braided High-Pressure Injection Lines	Polyurethane	1,200		High	Medium	10, 20, 30, 49	Braided polyurethane, FLL/rotating MLL connectors, braided polyurethane FLL/MLL connectors
Navilyst Medical	LPCIL: Low-Pressure Contrast Injection Line	PVC	500	0.089/0.159	Medium	High	10, 20, 30, 48, 60, 72	FLL to MLL, FLL to RA, MLL to MLL
	HPCIL: High-Pressure Contrast Injection Line		1,000	0.089/0.188	Low		10, 20, 30, 48, 60, 72, 80, 96	
	ClearaCIL High-Pressure Contrast Injection Line	Coextruded nylon/urethane	1,200	0.071/0.141	Medium	Medium	10, 20, 30, 48	FLL to MLL, FLL to RA
	flexCIL High-Pressure Contrast Injection Line	Braided polyurethane		0.071/0.142	High		4, 10, 20, 30, 48, 60, 72	
FLL, female luer lock; ID, inner diameter; MLL, male luer lock; OD, outer diameter; PVC, polyvinyl chloride; RA, rotating adapter.								